

## RANA T5 1200 S&S


RANA S 1200 White Bright Louvre 2x28W T5 840

0050265



### Product features

- Surface or Suspended T5 luminaire, 1183 x 187 x 47mm, White coated body, Bright Aluminium Reflector 98% reflectivity, 2 x 28W T5 lamps (included), Neutral White 4000K, Electronic Ballast, 64W, 4740lm, LOR 90%, Push-in Connector, IP20, IK07, Glow Wire test 960°C, UGR<13, LM65<1000 cd/m<sup>2</sup>.



### PRODUCT OVERVIEW

Product name	RANA S 1200 White Bright Louvre 2x28W T5 840
Technology	T5
Cap/Base	G5
Housing	Steel
Mount	Ceiling surface mounting, Suspended
Environment	Interior
General application	Education, Hospitality, Office, Retail
ETIM Class	EC002892
E-number FI	4289080
E-number Norway	3319606
Warranty	2 years
Fixture luminous flux (lm)	4740
Luminaire efficacy (lm/W)	74
LOR (%)	90
Colour temperature (K)	4000
Light colour	Neutral White
CRI (Ra)	85
Glare control	< 13
Light source included	0002767
Total power consumption (W)	64
Electrical protection	Class I
Control gear type	Electronic ballast
Control gear mounting	Integral
Dimmable	No
Housing colour	White
IP rating	IP20
IK rating	IK07
Product EAN number	5410288502656

## RANA T5 1200 S&S

*RANA S 1200 White Bright Louvre 2x28W T5 840*

0050265

### DATA TABLE

#### General data

<b>Product name</b>	RANA S 1200 White Bright Louvre 2x28W T5 840
<b>Technology</b>	T5
<b>Cap/Base</b>	G5
<b>Housing</b>	Steel
<b>Mount</b>	Ceiling surface mounting, Suspended
<b>Environment</b>	Interior
<b>General application</b>	Education, Hospitality, Office, Retail
<b>Performance ambient temperature Tq (°C)</b>	25
<b>ETIM Class</b>	EC002892
<b>E-number FI</b>	4289080
<b>E-number Norway</b>	3319606
<b>Warranty</b>	2 years

#### Optical data

<b>Fixture luminous flux (lm)</b>	4740
<b>Luminaire efficacy (lm/W)</b>	74
<b>LOR (%)</b>	90
<b>Colour temperature (K)</b>	4000
<b>Light colour</b>	Neutral White
<b>CRI (Ra)</b>	85
<b>Adjustable chromaticity</b>	N
<b>Distribution type</b>	Symmetric
<b>Glare control</b>	< 13

#### Electrical data

<b>Light source included</b>	0002767
<b>Total power consumption (W)</b>	64
<b>Mains voltage (V)</b>	220-240V
<b>Electrical protection</b>	Class I
<b>Control gear type</b>	Electronic ballast
<b>Control gear mounting</b>	Integral
<b>Transformer required</b>	Yes
<b>Dimmable</b>	No
<b>Glow Wire Test (°C)</b>	960
<b>Energy Efficiency Class (A-&gt;G) of contained light source</b>	F
<b>Nominal Frequency (Hz)</b>	50/60Hz

#### Physical data

<b>Housing colour</b>	White
<b>IP rating</b>	IP20
<b>IK rating</b>	IK07
<b>Reflector finish</b>	High-gloss
<b>Nominal Product Length (mm)</b>	1183
<b>Nominal Product Width (mm)</b>	187

## RANA T5 1200 S&S


RANA S 1200 White Bright Louvre 2x28W T5 840  
0050265

Nominal Product Height (mm)	46
Weight (kg)	3.34

### Packaging

Single packaging type	Carton
Product EAN number	5410288502656
Packaging single length / height (cm)	119.0
Packaging single width (cm)	5.5
Packaging single depth (cm)	19.5
DUN14 (outer)	05410288502656
Units per outer package	1
Packaging outer length / height (cm)	119.0
Packaging outer width (cm)	5.5
Packaging outer depth (cm)	19.5

## PHOTOMETRY



## TECHNICAL DRAWINGS

Dimensions		Length						Width					
		Side			Front			Side			Front		
Finning		1x28W	1x28W	1x28W	2x28W	2x28W	2x28W	1x28W	1x28W	1x28W	2x28W	2x28W	2x28W
Length (mm)		1183	1483	1183	1183	1483	1183	1483	1483	1183	1483	1183	1483
Width (mm)		167	167	167	167	167	167	167	167	167	167	167	167
Height (mm)		47	47	47	47	47	47	47	47	47	47	47	47
Finning		1x28W	2x28W	2x28W	2x28W	4x14W	4x14W	1x28W	1x28W	1x28W	2x28W	2x28W	2x28W
Length (mm)		1483	1483	1483	1483	1483	1483	1183	1183	1183	1483	1483	1483
Width (mm)		167	167	167	167	167	167	167	167	167	167	167	167
Height (mm)		47	47	47	47	47	47	47	47	47	47	47	47