

## Adjustable clamps

Depressed centre



### Version:

- Heat-treated steel
- Painted
- Single depressed centre



<b>Art. no.</b>	<b>26138 030</b>
<b>Slot width</b>	11 mm
<b>Length</b>	100 mm
<b>Suitable cheese-head screw DIN 912</b>	M10
<b>Slot length</b>	32 mm
<b>Clamping shoe height</b>	15 mm
<b>Clamping shoe width</b>	30 mm
<b>Height</b>	14 mm
<b>Width 3</b>	15 mm
<b>Height 2</b>	12 mm
<b>DIN</b>	6316

### EAN-Code

4020772071042