

Micrometer set



Application:

For measuring e. g. shaft diameters, external dimensions on workpieces etc.

Execution:

- Scale with anti-glare, brushed chromium plated finish
- Carbide measuring faces
- Friction coupling for consistent, repeatable measuring force

Delivery:

In a case, test report with declaration of conformity



Art. no.	31414 100
Brand	TESA
Manufacturer Part Number	00110113
Min./max. length measuring range	0-100 mm
Measuring spindle increments	0.5 mm
Spindle clamping	Yes
Number of bracket measuring screws	4
DIN	863
Calibration Group	On demand
Gross Weight	2.036 kg
Product Group	362

EAN

7630041104202