

TE Type T - Measuring tip

wired



Application:

The measuring tip with TE connector Type T is ideal for measuring temperatures in incoming goods. Ideal e.g. for measuring frozen goods between packages

Execution:

- Sensor type: TE Type T
- Measuring range: -50 to +350 °C
- Accuracy: $\pm 0.5^{\circ}\text{C}$ at -40 to +133 °C
- Accuracy: Class 1 in accordance with EN 60584-2 (remaining measuring range)
- Response time: 5 s
- Length/diameter of probe/sensor tube: 500 mm/1.5 mm
- Product/housing material: Stainless steel

Art. no.	46108 665
Brand	TESTO
Manufacturer Part Number	0628 0023
Sensor type	TE type T
Probe type	Food probe
Probe designation	Measuring tip
Min./max. temperature measuring range	-50 to 350 °C
Accuracy temperature	+/- 0.5 °C at -40 to +133 °C, Class 1 according to EN 60584-2 (remaining measuring range)
Response time sensor	5 s
Diameter probe tube	1.5 mm
Length sensor tube	500 mm
EN standard	60584-1
Material of housing	Stainless steel
Gross Weight	0.045 kg
Product Group	4CF



EAN

4029547004636