

8000 series shelf trolley, load capacity 250 kg, central brake

In 2 sizes and with 2, 3 and 4 load areas



Application:

Ideal as a transport and picking trolley for many different types of goods.

Execution:

- Electrolytically galvanised, highly stable tubular frame structure with front and rear grid
- Load areas made of laminated chipboard

Advantage:

- Continuously height-adjustable load areas
- Ergonomic - height-adjustable push handle
- Helps to transport goods more efficiently
- Central brake



Art. no.	50291 340
Brand	KONGAMEK
Manufacturer Part Number	KM8000-3XL-CL
Load-carrying capacity	250 kg
Load-carrying capacity of loading surfaces	125 kg
Colour	Silver coloured
Material of loading surface	Wood composite board
Number of loading surfaces	3
Loading surface length	1395 mm
ESD-capable	No
Loading-surface width	470 mm
Length	1395 mm
Width	470 mm
Height	1120 mm
Loading surface size	1395 x 470 mm
Surface	Zinc plated
Length x width x height	1395 x 470 x 1120 mm
With wheel lock	Yes
Wheel diameter	125 mm
Wheel width	32 mm
Material of wheel	TPE
Number of steering rollers	4
Made in	Sweden
Number of panels	2
Type	Central brake
Gross Weight	30.000 kg
Product Group	5AT

EAN

7350050356132