

Articulated hook wrenches

industrial version



Execution:

- Special steel
- Rounded edges
- With suspension hole
- Extended hook and shank
- Reinforced rivet
- With spring washer
- Surface annealed in burnished finish

Advantage:

- Longer shank for greater transferable torque
- Reinforced rivet for longer service life with greater force transmission
- Even movement with additional spring washer
- One-hand operation possible
- Excellent material strength with low-tension microstructure



Art. no.	52104 020
Brand	AMF
Manufacturer Part Number	51656
Suitable for nut type	Slotted nut DIN 1804, Bearing nut DIN 981
Suitable for min./max. nut male thread size	35-60 mm
Thickness	5 mm
Length	210 mm
Gross Weight	0.166 kg
Product Group	532

EAN

4020772051655