

MM 5-2 high-performance multi-purpose measuring instrument

TRUE RMS multimeter

BENNING

Application:

for use in industry, service and trade

Delivery:

Protective rubber frame, batteries, measuring leads, wire temperature sensor, bag



Art. no.	75024 215
Brand	BENNING
Manufacturer Part Number	44071
Model	MM 5-2
Display range	6000 digits
Measuring accuracy	+/- 0.5 %
Min./max. test voltage (DC)	100 μ V/DC-600 V/DC
Min./max. test voltage (AC)	100 μ V/AC-600 V/AC
Min./max. alternating current of measuring range	1 mA-10 A
Min./max. direct current of measuring range	0.1 μ A-10 A
Continuity testing	Yes
Diode testing	Yes
Min./max. electrical-resistance measuring range	100 mOhm-40 MOhm
Min./max. frequency	0.00001 / 50 kHz
Min./max. temperature measuring range	-40 to 400 °C
Volt sensor	Yes
Memory function	HOLD, PEAK
Measuring procedure	TRUE RMS
Overvoltage protection category	CAT IV/300 V, CAT III/600 V
Length x width x height	150 x 77 x 44 mm
EN standard	61010
Gross Weight	0.620 kg
Product Group	7AH

EAN

4014651440715