



product details

DULUX F 18W/840 2G10 FS1



Product description: DULUX F 18W/840 2G10 FS1
 Product code: 4050300333526
 Quantity: Folding carton box (FS) contains 1 Piece (PCE)

You can find this product in the eCatalog:
http://catalog.myosram.com?~language=EN&~country=COM&it_p=4050300333526

Applications	
Suitable for indoor	Yes

Categorizations	
SEG number	8330634
Sstl-Number	4934009

Certificates & Standards	
EEl - Energy Label	B

General Description	
Lamp mercury content	1.8 mg
Base (standard designation)	2G10
Recycling	Yes

Technical - Electrical Data	
Rated lamp efficacy (HF data)	Under clarification by authority and standardization body
Construction wattage	18
Rated lamp efficacy (standard condition)	61 lm/W
Operation mode LLMF/LSF	50 Hz
Nominal wattage	18 W

Technical - Geometries	
Overall length	128.30 mm
Diameter	17.50 mm
Tube diameter	17.5 mm
Length	122.00 mm
Length acc. to IEC standard	122 mm
Construction length	128.30 mm

Technical - Lifespan	
Rated lamp life time	8000 h
Nominal lamp life time	8000 h
Rated lamp survival factor 2000 h	0.99
Rated lamp survival factor 4000 h	0.99
Rated lamp survival factor 6000 h	0.97
Rated lamp survival factor 8000 h	0.85

Technical - Light Technical Data	
Rated color rendering index (Ra)	>=80
Nominal luminous flux	1100 lm
Luminous flux at 25 °C	1100 lm
Rated luminous flux	1100 lm





product details

DULUX F 18W/840 2G10 FS1

Technical - Light Technical Data	
Luminous flux	1100 lm
Light color	840
Rated color temperature	4000 K
Color rendering index Ra	80...89
Light color as per EN 12464-1	LUMILUX Cool White
Rated LLMF at 2000 h	0.85
Rated LLMF at 4000 h	0.78
Rated LLMF at 6000 h	0.76
Rated LLMF at 8000 h	0.76
Color rendering group	1B
Color temperature	4000 K

Technical - Temperatures	
Rated ambient temp.w.max.luminous flux	25.0 °C

Packaging units				
Product code	Packaging type and content	Dimensions in h x w x l	Gross weight	Volume
4050300333526	Folding carton box contains 1 Piece	86,000 mm x 25,000 mm x 145,000 mm	95,400 g (0,000 g)	0,312 Cubic dec.
4050300333533	Shipping carton box contains 10 Piece	150,000 mm x 105,000 mm x 280,000 mm	1.066,000 g (0,000 g)	4,410 Cubic dec.

OSRAM DULUX F lamps are new low-profile compact fluorescent lamps with high luminous efficacy. They are ideal for area lighting with 2 M and 3 M modular luminaires (200 and 300 mm sides), e.g. for square surface-mounted and recessed luminaires, low-profile wall and ceiling luminaires, downlights and uplights.

- High luminous efficacy: with QUICKTRONIC the OSRAM DULUX F 36 W has a 13 % higher luminous flux than two OSRAM DULUX L 18 W lamps
- Compact dimensions: only about half as long as an OSRAM DULUX L of comparable output
- The OSRAM DULUX F 36 W is easier to install and involves lower system costs than two OSRAM DULUX L 18 W lamps
- Can be used with the same HF control gear or conventional control gear as OSRAM DULUX L lamps of comparable output
- 4-pin plug-in 2G10 base

For more information on QUICKTRONIC electronic control gear go to www.osram.com/QUICKTRONIC.