

Bezeichnung

Maßzeichnung


Polzahl

von hinten verschraubbar


von vorn verschraubbar

Flanschdose, mit Litzen/von vorn verschraubbar, mit Litzen

3 x 0,25	09 3412 00 03		09 3412 86 03
4 x 0,25	09 3390 00 04		09 3390 86 04
6 x 0,14	09 3462 00 06		09 3462 86 06
8 x 0,14	09 3486 00 08		09 3486 86 08




von hinten verschraubbar




von vorn verschraubbar

Flanschdose, mit Litzen/von vorn verschraubbar, mit Litzen

3 x 0,25	09 3418 00 03		09 3418 86 03
4 x 0,25	09 3420 00 04		09 3420 86 04
5 x 0,25	09 3424 00 05		09 3424 86 05
6 x 0,14	09 3422 00 06		09 3422 86 06
8 x 0,14	09 3426 00 08		09 3426 86 08




von hinten verschraubbar



von vorn verschraubbar


Flanschdose, von vorn verschraubbar, tauchlöten

Polzahl	Kontaktlänge	Bestell-Nr.	
3	9,5 mm	09 3412 80 03	
	4,7 mm	09 3412 187 03	
	0,5 mm	09 3412 186 03	
4	9,5 mm	09 3390 80 04	
	4,7 mm	09 3390 187 04	
6	0,5 mm	09 3390 186 04	
	1,5 mm	09 3462 80 06	
8	1,5 mm	09 3486 80 08	



Flanschdose, von vorn verschraubbar, tauchlöten, mit Schirmblech


Polzahl	Bestell-Nr.
3	09 3418 81 03
4	09 3420 81 04
5	09 3424 81 05
6	09 3422 81 06
8	09 3426 81 08



Leiterplattendicke: 1,6 mm

Flanschdose, gewinkelt, von vorn verschraubbar, tauchlöten, mit Schirmblech


3	09 3418 82 03
4	09 3420 82 04
5	09 3424 82 05
6	09 3422 82 06



Leiterplattendicke: 1,6 mm

Flanschdose, tauchlöten, 6 mm/10 mm

Polzahl	6 mm	10 mm
3	99 3412 281 03	99 3412 280 03
4	99 3390 281 04	99 3390 280 04



Leiterplattendicke: 1,5 mm

