

# Crimp Fittings

# Press-armaturen


# Embouts sertis

# Raccordi a graffare

# Racores para presión

## FJB

J.I.C Female Swivel, 90° Elbow  
 JIC-Dichtkopf, 90° Krümmer  
 Femelle JIC coudé 90°  
 Femina girevole JIC a 90°  
 Hembra loca JIC acodado a 90°



Part Number	Part Number	Part Number	Thread T	Flange	Tube O.D.	ND	Hose Size	A	D	H	E Ø	HEX [1]	HEX [2]	K Ø
OTC Fitting	Skive Nipple	TTC Fitting						mm	mm	mm	mm			mm
1G4FJB4	1S4FJB4	1A4FJB4	7/16-20				-4	46,7	23,3	17,3	3,9	14		
1G5FJB4	1S5FJB4	1A5FJB4	1/2-20				-4	48,7	25,3	19,3	4,2	17		
1G5FJB5	1S5FJB5	1A5FJB5	1/2-20				-5	49,5	25,6	19,3	4,6	17		
1G6FJB5	1S6FJB5	1A6FJB5	9/16-18				-5	51,6	27,7	21,6	5,3	19		
1G6FJB6	1S6FJB6	1A6FJB6	9/16-18				-6	56,2	30,9	21,6	6,2	19		
1G8FJB6	1S8FJB6	1A8FJB6	3/4-16				-6	61,4	36,1	27,7	6,7	22		
1G8FJB8	1S8FJB8	1A8FJB8	3/4-16				-8	65,8	36,0	27,7	9,4	22		
1G10FJB8	1S10FJB8	1A10FJB8	7/8-14				-8	70,7	41,0	30,3	9,6	27		
1G10FJB10	1S10FJB10	1A10FJB10	7/8-14				-10	68,7	39,3	30,3	11,7	27		
1G12FJB10	1S12FJB10	1A12FJB10	1 1/16-12				-10	84,2	54,8	45,8	12,8	32		
1G12FJB12	1S12FJB12	1A12FJB12	1 1/16-12				-12	85,4	55,2	45,8	14,8	32		
1G16FJB12	1S16FJB12	1A16FJB12	1 5/16-12				-12	85,5	55,3	60,7	15,5	41		
1G12FJB16	1S12FJB16	1A12FJB16	1 1/16-12				-16	89,5	55,1	45,7	20,7	32		
1G16FJB16	1S16FJB16	1A16FJB16	1 5/16-12				-16	90,4	55,9	60,7	20,7	41		
1G20FJB20	1S20FJB20	1AP20FJB20*	1 5/8-12				-20	107,9	64,0	69,8	26,6	50		
		1AT20FJB20**	1 5/8-12				-20	107,9	64,0	69,8	26,6	50		

\* 1-wire  
 \*\* 2-wire

\* 1-wire  
 \*\* 2-wire

\* 1-wire  
 \*\* 2-wire

\* 1-wire  
 \*\* 2-wire

\* 1-wire  
 \*\* 2-wire