


Steckverschraubungen QS, Quick Star

Datenblatt

L-Steckverschraubung QSL

360° schwenkbar
Außengewinde
mit Außensechskant



Abmessungen und Bestellangaben													
Anschluss	Nennweite	Schlauch- Außen-∅	D5 ∅	H1	H2	H3	L1	≈∅	Gewicht/ Stück [g]	Teile-Nr.	Typ	PE*	
D1	[mm]	D2											
R-Gewinde													
R ¹ / ₈	2,3	4	10	23,5	8	19,5	18,5	10	12	153045	QSL- ¹ / ₈ -4	10	
										130728	QSL- ¹ / ₈ -4-100	100	
	3,6	6	12,5	25	8	21	20	12	14	153046	QSL- ¹ / ₈ -6	10	
											130729	QSL- ¹ / ₈ -6-100	100
	4,6	8	14,5	28	8	24	23	14	18	153048	QSL- ¹ / ₈ -8	10	
										130730	QSL- ¹ / ₈ -8-50	50	
	5,3	10	17,5	33	8	29,1	26,2	17	31	190658	QSL- ¹ / ₈ -10	10	
R ¹ / ₄	2,3	4	10	26,3	11	20,3	18	14	21	190659	QSL- ¹ / ₄ -4	10	
	3,6	6	12,5	28	11	22	20	14	22	153047	QSL- ¹ / ₄ -6	10	
										130731	QSL- ¹ / ₄ -6-100	100	
	4,6	8	14,5	31	11	25	23	14	24	153049	QSL- ¹ / ₄ -8	10	
										130732	QSL- ¹ / ₄ -8-50	50	
	6,2	10	17,5	37	11	30,5	26,5	17	34	153051	QSL- ¹ / ₄ -10	10	
										130733	QSL- ¹ / ₄ -10-50	50	
	7,7	12	21	38	11	32	29,5	21	50,5	164981	QSL- ¹ / ₄ -12	10	
										130734	QSL- ¹ / ₄ -12-20	20	
R ³ / ₈	3,6	6	12,5	29,8	12	23,7	19,7	17	35	190660	QSL- ³ / ₈ -6	10	
	4,6	8	14,5	33	12	26,5	23	17	37	153050	QSL- ³ / ₈ -8	10	
										130735	QSL- ³ / ₈ -8-50	50	
	6,2	10	17,5	40	12	32	26,5	17	42	153052	QSL- ³ / ₈ -10	10	
										130736	QSL- ³ / ₈ -10-20	20	
	7,7	12	21	41,5	12	34	29,5	21	51,5	153053	QSL- ³ / ₈ -12	10	
										130737	QSL- ³ / ₈ -12-20	20	
	10,1	16	25	47	11	40,7	33,5	22	74	164958	QSL- ³ / ₈ -16	1	
R ¹ / ₂	6,2	10	17,5	40	15	31,9	26,2	21	64	190661	QSL- ¹ / ₂ -10	1	
	7,7	12	21	41,5	15	33,5	29,5	21	66	153054	QSL- ¹ / ₂ -12	1	
										130738	QSL- ¹ / ₂ -12-20	20	
	10,9	16	25	51	15	42,9	33,5	22	79	153055	QSL- ¹ / ₂ -16	1	
										130739	QSL- ¹ / ₂ -16-20	20	

* Packungseinheit in Stück