

RMME 11/230 AC INPUT RELAY


IN: 230 VAC/DC - OUT: 125 VAC/DC / 1 A


1 relay; 1 NO contact

1 A

230 V AC

Screw terminals

[Link to Product](#)**Illustration**



Product may differ from Image

Utilization category

AC-12	0.5 A (50 V AC)
AC-15	0.25 A (50 V AC)

Input

Connection voltage - current	230 V AC (195...253 V AC) - 6 mA
LED display	LED (yellow)

General data

Mech./ elect. life	100.000.000 switching cycles/load dependent
Test isolation voltage	1.5 kV
Mounting method	DIN-rail mountable TH35 or G32 (EN 60715)
Temperature range	-20...+60 °C
Dimensions H × W × D	56×12×64 mm

Output

Switching voltage	max. 125 V AC/DC
Switching current per output	max. 1 A
Min. load current	1 mA
Power rating (voltage dependent)	max. 60 VA/30 W
Switching frequency	max. 15 Hz
Contact material	Pd Ni-Au Rh
Energize/release/contact bounce time	10/10/1 ms

Commercial data

country of origin	CZ
customs tariff number	85364900
minimum order quantity	1