




Dimensions



Model Number

V3-GM-0,3M-PUR-V11-G

Connection cable, M8 to M12, PUR cable, 3-pin

Features

- Knurled nut suitable for tool assembly
- Immunity to vibration, with mechanical latching
- Gold plated contacts
- Halogen-free
- Suitable for 2- and 3-wire technology

Technical data

General specifications

Number of pins 3

Electrical specifications

Operating voltage U_B max. 60 V AC/DC

Test voltage $> 1500 V_{eff} AC$

Operating current I_B max. 3 A

Volume resistance $< 5 m\Omega$

Ambient conditions

Ambient temperature cable, fixed: -40 ... 80 °C (-40 ... 176 °F)
cable, flexing: -20 ... 80 °C (-4 ... 176 °F)

Pollution Degree 3

Mechanical specifications

Contact elements spring-loaded contact socket

Pin diameter 1 mm

Degree of protection IP67

Material

Contacts CuSn / Au

Contact surface Au

Body TPU, black

Cable PUR

Slotted nut Diecast zinc

Sleeve connector Diecast zinc

Core insulation PP

Cable fine-strand, flexible

Sheath diameter $\varnothing 4.3 mm$

Bending radius $> 15 x$ cable diameter, induced
 $> 8 x$ cable diameter, fixed


Color grey

Cores 3 x 0.25 mm²

Conductor construction 14 x 0.15 mm \varnothing

Length L 0.3 m

Electrical connection



Release date: 2014-11-21 15:48 Date of issue: 2014-11-21 241667_eng.xml