


## Product information


# 97 32 240

- With threaded holes for cutting copper and brass screws threaded M 2.6 / M 3 / M 3.5 / M 4 and M 5
- Bolted joint for higher stability and even movement
- Special steel, high-strength



## Crimping Pliers




General	
Article No.	97 32 240
EAN	4003773079491
Pliers	black lacquered
Handles	with multi-component grips
Weight	264 g
Dimensions	240 x 62 x 25 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details	
	
Application	insulated terminals + cable connectors
Capacity in square millimetres	0.5 — 6.0 mm <sup>2</sup>
Number of crimping positions	3
AWG	20 — 10

technical change and errors excepted




97 21 215



97 21 215 B



97 21 215 B



97 21 215 B



97 21 215 B

