


Coaxial Cable Connector 16_MM CX-50-2-2/111_O

Description

Right angle cable plug

Interface standards
SUHNER-MM CX



Technical Data

Electrical Data

Impedance 50 Ω
Interface frequency max. 6 GHz

Mechanical Data

Centre contact soldered
Outer contact crimped
Weight 0.0008 kg

Environmental Data

Operating temperature -55 °C to 155 °C
2011/65/EU (RoHS - including
2015/863 and 2017/2102) compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	Gold Plating (without Nickel underplating)
Body	Brass	Gold Plating (without Nickel underplating)
Insulator	PFA / PTFE	
Crimp ferrule	Copper	Gold Plating (without Nickel underplating)

Related Documents

Outline drawing DOU-00007188
Catalogue drawing DOU-00006005
Assembly instruction DOC-0000241538

Ordering Information

Bulk 100 pcs package 16_MM CX-50-2-2/111_OH
Single package 16_MM CX-50-2-2/111_OE

Additional Information

Suitable cables K_02252_D, ENVIROFLEX_316_D, G_02232_D