

## D-Sub, FE AWG 20-24 crimp cont



Image is for illustration purposes only. Please refer to product description.

Part number	09 67 000 8476
Specification	D-Sub, FE AWG 20-24 crimp cont
HARTING eCatalogue	<a href="https://b2b.harting.com/09670008476">https://b2b.harting.com/09670008476</a>

### Identification

Category	Contacts
Series	D-Sub
Identification	Standard
Type of contact	Crimp contact

### Version

Gender	Female
Manufacturing process	Turned contacts

### Technical characteristics

Conductor cross-section	0.25 ... 0.52 mm <sup>2</sup>
Conductor cross-section	AWG 24 ... AWG 20
Contact resistance	≤10 mΩ
Stripping length	4 mm
Performance level	1 acc. to CECC 75301-802

### Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Noble metal over Ni
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption



**Pushing Performance**  
Since 1945

## Material properties

China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	339476a1-86ba-49e9-ab4b-cd336420d72a
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

## Commercial data

Packaging size	100
Net weight	0.21 g
Country of origin	Switzerland
European customs tariff number	85366990
GTIN	5713140087279
eCl@ss	27440204 Contact for industrial connectors