

shrink-fit extensions with IC

with straight shank

ATORN®

Application

For extending and reducing to smaller diameters.

Version

- With 4.5 ° angle
- Clamping diameter for shaft tolerance h 6
- Workpiece stop screw with 10 mm adjustment travel



Art. No.	23431 637
Clamping diameter	8 mm
Outer diameter	25 mm
Length	150 mm
Max. clamp in depth	36 mm
Min. clamp in depth	26 mm
Max. adjustment travel	10 mm
Setting screw size	M6
Width across flats	3 mm

EAN-Code

4050293418187