

push rod clamp with variable clamping height

with angular base



Application:

Quick-action clamp with infinitely adjustable balancing function for workpieces with different clamping widths.

Version:

- galvanised and passivated.
- ergonomic, oil-resistant handle with large hand rest and soft components.
- protection against the loss of the clamping screw on the end of the clamping arm. complete with zinc-plated clamping bolt
- Size 15 clamping bolt M6 x 29 mm
- Size 25 clamping bolt M8 x 38 mm

Advantage:

- variable clamping height, for clamping different workpieces
- used for small lot sizes
- infinitely adjustable clamping force
- ergonomic 2 component handle
- protection against loss on clamping arm



| | |
|---------------------------------------|------------------|
| Art. no. | 26217 120 |
| Size | 25 |
| Distance | 11.8 mm |
| Min./max. clamping width | 58-83 mm |
| Min./max. length | 20.5-30 mm |
| Drill hole | 6.5 mm |
| Drill hole 2 | 6.5 mm |
| Length 2 | 27 mm |
| Height | 84 mm |
| Overall height of lower handle | 119 mm |
| Clamping stroke | 25 mm |
| Overall height of upper handle | 238 mm |
| Thread dimension | M8 |
| Distance 2 | 10.6 mm |
| Length | 236 mm |
| Base plate width | 57 mm |
| Hole distance 3 | 38.1 mm |
| Base plate length | 51 mm |
| Tension force | 3 kN |
| Height 2 | 25 mm |
| Height 3 | 35 mm |

EAN-Code

4020772003708