

Stepladders

Single-sided access



Version:

- Patented step design: robust, stable, durable, flanged step-rail connection
- High-strength Perlon straps with sewn-in fixing clip to prevent splay (7 or more steps)
- Closed step profile and integrated guide tube
- Optimum platform stability thanks to extruded aluminium profile
- Two bridge lifts made of extruded sections
- Practical storage tray with lots of space for tools and small parts

Advantage:

- Stable footing thanks to non-slip plastic shoes
- Large-surface standing platform with anti-slip grooves

| | |
|---|------------------|
| Art. no. | 50260 540 |
| Number of steps (including platform) | 1 x 3 |
| Working height | 2.6 m |
| Length | 1.34 |
| Platform height | 0.61 m |
| Pedestal width | 0.42 m |
| Weight | 4.8 kg |
| Accessibility | One-sided |
| Material | Aluminium |
| With storage tray | Yes |
| Folding | Yes |
| EN standard | 131 |



EAN-Code

4003866424535