



ALUSPIEGEL 60° 350mA CRI90 LED POWER MODUL 10W 2700K

Article nr.: 88808

LED-module 10W · 50 mm with reflector · more than 800 lumens · · 1 x power LED array Bridgelux (USA) 10W watts · dimmable · Light colours: 2700K, 3000K · CRI 80 / CRI 90 · Lifetime L70B50: >= 50.000 h · for operation with constant current converter 350mA · Excellent heat dissipation due to optimised aluminium heatsink · Aluminium reflector with halogen appearance and uniform light distribution, · beam angle 43° and 60° · energy efficiency class: F

TECHNICAL DATA

Unit Code	pcs
BAR code	4012094888088
Length	70.00 mm
Outer diameter	50 mm
LED colour	UWW ca. 2700K
Lightoutput per fixture	838.00 lm
Lamp	Inklusive LED
IP rating	20
Beam angle	60 °
Power	10 W





ALUSPIEGEL 60° 350mA CRI90 LED POWER MODUL 10W 2700K

Article nr.: 88808

TECHNICAL DATA

Current mA	350 mA
Amount of LED	1
Material	Aluminium
Energy efficiency class	EEK-Label_F
CRI	≥ 90
Lifetime L70B50	50.000 h





**ALUSPIEGEL 60° 350mA CRI90 LED
POWER MODUL 10W 2700K**

Article nr.: 88808

TECHNICAL DRAWING

