

## Socket sets and sockets


6,3  
1/4"



DIN  
3120

ISO  
1174-1

### 44KTXB Screwdriver sockets


- with hollow point
- for inside TORX® screws (TORX® TAMPER RESISTANT)
- Chrome Alloy Steel, chrome plated





| Code             | size       | mm  | L <sub>1</sub><br>mm | L <sub>2</sub><br>mm | d<br>mm |  g |  |
|------------------|------------|-----|----------------------|----------------------|---------|---|---|
| <b>0135 1008</b> | <b>T8</b>  | 2.3 | 28                   | 16                   | 11.6    | 10  | 5   |
| <b>0135 1009</b> | <b>T9</b>  | 2.5 | 28                   | 16                   | 11.6    | 10  | 5   |
| <b>0135 1010</b> | <b>T10</b> | 2.7 | 28                   | 16                   | 11.6    | 10  | 5   |
| <b>0135 1015</b> | <b>T15</b> | 3.3 | 28                   | 16                   | 11.6    | 10  | 5   |
| <b>0135 1020</b> | <b>T20</b> | 3.8 | 28                   | 16                   | 11.6    | 10  | 5   |
| <b>0135 1025</b> | <b>T25</b> | 4.4 | 28                   | 16                   | 11.6    | 11  | 5   |
| <b>0135 1027</b> | <b>T27</b> | 5.0 | 28                   | 16                   | 11.6    | 10  | 5   |
| <b>0135 1030</b> | <b>T30</b> | 5.5 | 28                   | 16                   | 11.6    | 11  | 5   |
| <b>0135 1040</b> | <b>T40</b> | 6.6 | 28                   | 16                   | 11.6    | 10  | 5   |

### 44P Screwdriver sockets


- for recessed head screws Phillips-Recess®
- tips to DIN 5260
- Chrome Alloy Steel, chrome plated





| Code            | PH<br>size | L <sub>1</sub><br>mm | L <sub>2</sub><br>mm | d<br>mm |  g |  |
|-----------------|------------|----------------------|----------------------|---------|---|---|
| <b>01290001</b> | <b>1</b>   | 28                   | 16                   | 11.6    | 12  | 5   |
| <b>01290002</b> | <b>2</b>   | 28                   | 16                   | 11.6    | 11  | 5   |
| <b>01290003</b> | <b>3</b>   | 28                   | 16                   | 11.6    | 12  | 5   |
| <b>01290004</b> | <b>4</b>   | 28                   | 16                   | 11.6    | 14  | 5   |

### 44PZ Screwdriver sockets

- for POZIDRIV/SUPADRIV® screws
- Chrome Alloy Steel, chrome plated




| Code            | PZ<br>size | L <sub>1</sub><br>mm | L <sub>2</sub><br>mm | d<br>mm |  g |  |
|-----------------|------------|----------------------|----------------------|---------|---|---|
| <b>01300001</b> | <b>1</b>   | 28                   | 16                   | 11.6    | 10  | 5   |
| <b>01300002</b> | <b>2</b>   | 28                   | 16                   | 11.6    | 11  | 5   |

### 40CL Clip strips


- for socket retention
- supplied without sockets



| Code            | size     | L<br>mm |  g |
|-----------------|----------|---------|---|
| <b>80400001</b> | <b>1</b> | 200     | 36  |
| <b>80400002</b> | <b>2</b> | 300     | 52  |

## Drive tools and accessories



- 1/4" □
- finish: Chrome Alloy Steel, chrome plated



### 411 Ratchet, fine tooth

- reversible
- 60 teeth
- with 2-component handle
- for use in confined spaces, re-engages after movement of 6°
- DIN 3122/ISO 3315





| Code            | L<br>mm | b<br>mm | a<br>mm |  g |  |
|-----------------|---------|---------|---------|---|---|
| <b>11231011</b> | 118     | 24      | 19.5    | 100   | 1   |


### 415 Ratchet

- reversible
- 22 teeth
- with 2-component handle
- DIN 3122/ISO 3315





| Code            | L<br>mm | b<br>mm | a<br>mm |  g |  |
|-----------------|---------|---------|---------|---|---|
| <b>11111010</b> | 117     | 22      | 13      | 80  | 5   |





### 415QR QuickRelease ratchet

-  reversible
- 22 teeth
- with QuickRelease safety lock
- with 2-component handle
- DIN 3122/ISO 3315
- registered design





| Code            | L<br>mm | b<br>mm | a<br>mm |  g |  |
|-----------------|---------|---------|---------|---|---|
| <b>11110020</b> | 117     | 22      | 13      | 79  | 1   |

### 415QR N QuickRelease ratchet, fine tooth

-    
- reversible
- 80 teeth
- with QuickRelease safety lock
- with 2-component handle
- for use in confined spaces, re-engages after movement of 4.5°
- construction without screws prevents foreign object damage
- DIN 3122/ISO 3315
- registered design



| Code            | L<br>mm | b<br>mm | a<br>mm |  g |  |
|-----------------|---------|---------|---------|---|---|
| <b>11111020</b> | 117     | 22.6    | 10.7    | 79  | 1   |