

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2147632115](#)
Status: **Active**
Overview:
Description: Pre-Crimped Lead Micro-Fit 3.0 Male-to-Pigtail, Tin (Sn) Plated, 450.00mm Length, 20 AWG, Red

General

| | |
|------------------------|-------------------------------|
| Product Family | Cable Assemblies |
| Series | 214763 |
| Application | Power, Wire-to-Wire |
| Assembly Configuration | Pre-crimped Lead Only |
| Connector to Connector | Micro-Fit 3.0 Crimp Terminals |
| Overview | precrimped_leads |
| Product Name | Micro-Fit 3.0 |
| UPC | 193264575312 |

Physical

| | |
|--------------------------------|----------------------|
| Cable Length | 450.00mm |
| Circuits (Loaded) | 1 |
| Color - Resin | Red |
| Gender | Male-Pigtail |
| Material - Metal | Phosphor Bronze |
| Material - Plating Mating | Tin |
| Material - Plating Termination | Tin |
| Net Weight | 3.157/g |
| Plating min - Mating | 1.016µm |
| Plating min - Termination | 1.016µm |
| Single Ended | Yes |
| Termination Interface: Style | Crimp or Compression |
| Wire Insulation Diameter | 1.85mm max. |
| Wire Size AWG | 20 |
| Wire/Cable Type | UL 10002 |

Electrical

| | |
|-------------------------------|------|
| Current - Maximum per Contact | 8.5A |
|-------------------------------|------|

Material Info

Reference - Drawing Numbers

| | |
|---------------|----------------|
| Sales Drawing | 2147631111-000 |
|---------------|----------------|

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)4578-DC (25
June 2020)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[214763](#) Series

Use With

Micro-Fit 3.0 Plug Housings [43020](#) , [43640](#)

Micro-Fit BMI Plug Housings [44300](#) ,
[46625](#)