

Spoked Handwheels DIN 950 AL with Smooth Rim and Slanted Spokes

Material: Aluminium, wheel rim ground and high-gloss finish.


Number of spokes:

3 spokes for sizes up to Ø 200.

5 spokes for sizes from Ø 225.

Version B/A: Borehole without keyway.

Version N/A: With keyway according to DIN 6885-1.



Ordering Details: e.g.: Product No. 670 008 00, Spoked Handwheel DIN 950 Al, Vers. B/A, 80 mm

Product No. Vers. B/A	Product No. Vers. N/A	d ₁ mm	d ₂ ^{H7} mm	d ₃ [*] mm	l ₁ mm	l ₂ mm	Weight kg
670 008 00	670 008 01	80	10	26	29	16	0,15
670 010 00	670 010 01	100	12	28	33	17	0,19
670 012 00	670 012 01	125	13	30	36	18	0,29
670 014 00	670 014 01	140	14	32	39	19	0,36
670 016 00	670 016 01	160	15	34,5	40	20	0,52
670 018 00	670 018 01	180	16	38,5	43	22	0,70
670 020 00	670 020 01	200	18	42,5	45	24	0,89
670 022 00	670 022 01	225	20	43	48	26	1,20
670 025 00	670 025 01	250	22	48,5	50	28	1,60
670 028 00	670 028 01	280	24	53	53	30	2,00
670 032 00	670 032 01	315	26	56	56	33	2,46

* Hub diameter bigger than DIN 950.

Spoked Handwheels DIN 950 AL with Smooth Rim and Slanted Spokes, with threaded lug.

Material: Aluminium, wheel rim ground and high-gloss finish.

Number of spokes:


3 spokes for sizes up to Ø 200.

5 spokes for sizes from Ø 225.

Version B/G: Borehole without keyway.

Version N/G: With keyway to DIN 6885-1.

The handle has to be ordered separately.



Ordering Details: e.g.: Product No. 670 108 00, Spoked Handwheel DIN 950 Al, Vers. B/G, 80 mm

Vers. N/G. Handle has to be ordered separately.

Product No. Vers. B/G	Product No. Vers. N/G	d ₁ mm	d ₂ ^{H7} mm	d ₃ [*] mm	l ₁ mm	l ₂ mm	Gewicht kg	Product No.	
								Matching revolving alumin. handle** rigid DIN 39	rotatable DIN 98
670 108 00	670 108 01	80	10	26	29	16	0,15	662 316 00	663 316 00
670 110 00	670 110 01	100	12	28	33	17	0,19	662 316 00	663 316 00
670 112 00	670 112 01	125	13	30	36	18	0,29	662 320 00	663 320 00
670 114 00	670 114 01	140	14	32	39	19	0,36	662 320 00	663 320 00
670 116 00	670 116 01	160	15	34,5	40	20	0,52	662 325 00	663 325 00
670 118 00	670 118 01	180	16	38,5	43	22	0,70	662 325 00	663 325 00
670 120 00	670 120 01	200	18	42,5	45	24	0,89	662 325 00	663 325 00
670 122 00	670 122 01	225	20	43	48	26	1,20	662 325 00	663 325 00
670 125 00	670 125 01	250	22	48,5	50	28	1,60	662 332 00	663 332 00
670 128 00	670 128 01	280	24	53	53	30	2,00	662 332 00	663 332 00
670 132 00	670 132 01	315	26	56	56	33	2,46	662 332 00	663 332 00

* Hub diameter bigger than DIN 950.

** Handles page 849.