

19" complete chassis from aluminium, plain top cover and base plate



Photo shows 1 U

Part no.: 20860-608

Features:

- Complete chassis from aluminium
- Detachable rear panel for easy machining
- EMC shielding of approx. 30 dB(A) at 1 GHz (without additional shielding material)
- In accordance with standard IEC 60297-3-100, -101, -105




NEW PRODUCT



Technical information:

Description	Height	Height H	Depth T
Solid top cover and base plate	3 U	132.6 mm	340 mm



h = clear height (overall) (H - 8.1 mm)
 b = clear installation width = 403 mm

Downloads:

[3D PDF \(STEP/DWG/DXF/PDF\)](#) (Log in Required)

[User manual](#) (Log in Required)

[EMC / HF test report](#) (Log in Required)

To gain access to the additional information you must [Log in](#).
 If you do not yet have a user name, you may [Register here](#).

Delivery comprises: Kit

Item	Qty	Description
1	1	Front panel, Al extrusion, 3 mm; front and rear side of front panels clear passivated
2	1	Rear panel, Al, 2 mm, etched
3	1	Base plate, plain, Al, 1 mm
4	1	Cover plate, plain, Al, 1 mm
5	2	Side panel, Al extrusion, raw; with grooves for threaded insert (2 × 7)
6	1	Assembly kit

Accessories:

Part no.	Description	
20860-130	EMC gasketing kit Silicone/nickel gasket 2100 mm for contacting side panel/cover plate; Seal, stainless steel, for front panel/cover plate, 1 kit	<input type="button" value="Add to basket"/>

20860-258

Front handles
incl. assembly kit for 3 U, Al extrusion, anodised, PU
2 pieces

Add to basket