

T-slot bolts



Application:

For clamping workpieces on machine tables.

Execution:

- Tempered
- Rolled thread
- Forged
- With milled groove guide
- M8 to M12, strength class 10.9
- M16 to M24, strength class 8.8
- DIN 787



Art. no.	26200 640
Brand	AMF
Manufacturer Part Number	84418
DIN	787
Thread dimension	M16
Groove width	18 mm
Length excluding head	125 mm
Outer diameter	17.7 mm
Thread length	85 mm
Length of head	28 mm
Head height	10 mm
Gross Weight	0.346 kg
Product Group	260

EAN

4020772084417