


# PRODUCT SPECIFICATION

<b>Brand</b>	C.K
<b>Product Range</b>	Auger Bits
<b>Catalogue number</b>	3031,3033, 3034
<b>Date</b>	09/07/2008

<b>Range Description</b> A range of professional quality Auger bits				
<b>Features</b> <ul style="list-style-type: none"> <li>• High carbon steel, hardened and precision ground for fast clean hole cutting</li> <li>• Screw tip for precise hole starts</li> <li>• Combination shank suitable for hand and power drills</li> </ul>				
Item Number	Item Description (Drill bits size = Diameter x working length x overall length)	EAN No	Commodity code	Carton Qty
T3031 06	Auger Bit Standard 6x90x160mm	5013969003567	82075090	6
T3031 08	Auger Bit Standard 8x100x170mm	5013969003574	82075090	6
T3031 10	Auger Bit Standard 10x120x190mm	5013969003581	82075090	6
T3031 13	Auger Bit Standard 13x120x190mm	5013969003604	82075090	6
T3031 16	Auger Bit Standard 16x130x200mm	5013969003611	82075090	6
T3031 20	Auger Bit Standard 20x130x200mm	5013969703696	82075090	6
T3031 22	Auger Bit Standard 22x140x210mm	5013969003635	82075090	6
T3031 25	Auger Bit Standard 25x140x210mm	5013969003642	82075090	6
T3031 30	Auger Bit Standard 30x140x210mm	5013969036220	82075090	6
T3031 32	Auger Bit Standard 32x140x210mm	5013969003659	82075090	6
T3033 13	Auger Bit Short 13x50x100mm	5013969003734	82075090	6

T3033 16	Auger Bit Short 16x70x120mm	5013969003741	82075090	6
T3033 20	Auger Bit Short 20x80x130mm	5013969703702	82075090	6
T3033 22	Auger Bit Short 22x80x130mm	5013969003765	82075090	6
T3033 25	Auger Bit Short 25x80x130mm	5013969003772	82075090	6
T3033 32	Auger Bit Short 32x80x140mm	5013969003789	82075090	6
T3034 10	Auger Bit Long 10x220x300mm	5013969003673	82075090	6
T3034 13	Auger Bit Long 13x220x300mm	5013969003680	82075090	6
T3034 16	Auger Bit Long 16x220x300mm	5013969003697	82075090	6
T3034 20	Auger Bit Long 20x220x300mm	5013969703719	82075090	6
T3034 22	Auger Bit Long 22x220x300mm	5013969003710	82075090	6
T3034 25	Auger Bit Long 25x220x300mm	5013969003727	82075090	6

Technical product information	
Standards compliance	
User health and safety information	Users and bystanders are advised to wear safety goggles
RoHS/WEEE compliance	This product range does not fall within the scope of RoHS or WEEE regulations
Material safety data	None applicable
Warranty	C.K Drills are guaranteed for life against imperfect materials or workmanship Normal wear and tear or damage caused through inappropriate use is not covered
Country of origin	Taiwan

## Dimensional details

Item	Product only				Product on primary packaging			
	Width mm	Depth mm	Height mm	Net weight g	Width mm	Depth mm	Height mm	Gross weight g
T3031 06	6	6	160	22	50	13	260	40
T3031 08	8	8	170	38	50	13	260	56
T3031 10	10	10	190	52	50	13	260	70
T3031 13	13	13	190	82	50	20	285	100
T3031 16	16	16	200	110	50	20	285	126
T3031 20	20	20	200	174	50	32	285	194
T3031 22	22	22	210	202	50	32	285	222
T3031 25	25	25	210	274	50	32	285	284
T3031 30	30	30	210	352	50	34	285	370

T3031 32	32	32	210	406	50	34	285	424
T3033 13	13	13	100	34	50	20	210	48
T3033 16	16	16	120	58	50	20	210	72
T3033 20	20	20	130	116	50	32	210	146
T3033 22	22	22	130	134	50	32	210	146
T3033 25	25	25	130	158	50	32	210	174
T3033 32	32	32	140	262	50	35	210	272
T3034 10	10	10	300	76	50	20	375	104
T3034 13	13	13	300	116	50	20	375	136
T3034 16	16	16	300	188	50	28	375	208
T3034 20	20	20	300	280	50	28	375	304
T3034 22	22	22	300	322	50	28	375	346
T3034 25	25	25	300	404	50	28	375	428

Item	Shelf box (secondary packaging)				Euro Pallet data Wi x Hi	
	Width mm	Depth mm	Height mm	Gross weight g	No of cartons on base	Number of rows high
T3031 06	115	295	40	312		
T3031 08	115	295	40	400		
T3031 10	115	295	40	488		
T3031 13	115	295	40	668		
T3031 16	135	325	75	880		
T3031 20	135	325	75	1290		
T3031 22	135	325	75	1456		
T3031 25	135	325	75	1835		
T3031 30	135	325	75	2344		
T3031 32	135	325	75	2668		
T3033 13	125	230	80	420		
T3033 16	125	230	80	564		
T3033 20	125	230	80	875		
T3033 22	125	230	80	875		
T3033 25	125	230	80	1176		
T3033 32	125	230	80	1764		
T3034 10	130	400	65	750		
T3034 13	130	400	65	942		

T3034 16	130	400	65	1374		
T3034 20	130	400	65	1975		
T3034 22	130	400	65	2202		
T3034 25	130	400	65	2694		

## Packaging waste details

Item	Primary Packaging				Secondary packaging			
	Plastic g	Use	Card g	Use	Plastic g	Use	Card g	Use
T3031 06	8	Blister	10	Card			68	Carton
T3031 08	8	Blister	10	Card			68	Carton
T3031 10	8	Blister	10	Card			68	Carton
T3031 13	8	Blister	10	Card			68	Carton
T3031 16	8	Blister	10	Card			124	Carton
T3031 20	8	Blister	10	Card			124	Carton
T3031 22	8	Blister	10	Card			124	Carton
T3031 25	8	Blister	10	Card			124	Carton
T3031 30	10	Blister	10	Card			124	Carton
T3031 32	10	Blister	10	Card			124	Carton
T3033 13	6	Blister	8	Card			132	Carton
T3033 16	6	Blister	8	Card			132	Carton
T3033 20	6	Blister	8	Card			132	Carton
T3033 22	6	Blister	8	Card			132	Carton
T3033 25	6	Blister	8	Card			132	Carton
T3033 32	8	Blister	8	Card			132	Carton
T3034 10	10	Blister	14	Card			126	Carton
T3034 13	10	Blister	14	Card			126	Carton
T3034 16	10	Blister	14	Card			126	Carton
T3034 20	10	Blister	14	Card			126	Carton
T3034 22	10	Blister	14	Card			126	Carton
T3034 25	10	Blister	14	Card			126	Carton