


Type Designation	6103
System	Lithium / Iron Disulfide (Li/FeS ₂)
Shelf Life (Coding)*	10 years
Nominal Voltage [V]	1.5
Typical Capacity C [mAh]	1100
Permissible Temperature Range	- 40 °C ... 50 °C
Weight, approx. [g]	7,3



Dimensions [mm]	min:	max:
Ø	9.5	10.5
A	-	44.5
B	43.5	-
F	-	3.8
G	0.8	-

Typical Capacities (at 20°C):

Discharge Type	Load	End Voltage[V]	1.05
2S/28S, 5M/H Digital Camera shots**	1200/650 mA	Pulse [n]	118
Discharge Type	Load	End Voltage[V]	0.9
10S/M, 1H/D, 7D/W Photo Flash	600 mA	Pulse [n]	653
Discharge Type	Load	End Voltage[V]	1.0
1H/D, 7D/W Tape**	100 mA	Time [h]	11,5

(** ANSI C18.3M)

No publication or circulation of data to third parties without consent of VARTA Consumer Batteries

* In consideration of typical loss of capacity at storage and application.