

LD0425x1-C700



Product Code:

LD0425x1-C700

| Electrical Data | |
|-------------------------|-----------|
| Mains Input Voltage (V) | 230 |
| Input Voltage Range (V) | 180-260 |
| Output Voltage (V) | DC 30-43V |
| Output Current (mA) | 700 |
| Power Factor | >0.9 |
| Product Data | |
| Lamp Base | N/A |
| Product Wattage (W) | n/a |
| Max. System Wattage (W) | 31 |
| Colour Temperature (K) | n/a |
| Dimmable | No |
| Weight (g) | 190 |
| Performance Data | |
| Rated Life (hrs) | 50000 |
| Product Dimensions | |
| Length (mm) | 123 |
| Width (mm) | 79 |
| Height (mm) | 35 |

Product Code: LD0425x1-C700

MEGAMAN® 2005-2018. All Rights Reserved.
This document is for informational purpose only.

MEGAMAN® reserves the right to make changes from time to time in the interest of product developments without prior notification to any products herein.

www.megaman.cc