





RoHS Compliant



Item description

- M12 sensor/actuator box, 6-way
- 5-pole (2 signals per contact)
- M23 connector (19-pole)

—



- Green LED operating indicator
- Yellow LED status indicator
- incl. markers (10 pcs)
- incl. M12 protective caps (2 pcs)

Data

Technical Data

Contact resistance max.	0.01 Ω
Supply voltage	DC 10 ... 30 V; Bemessungsspannung: 32 V ~ eff.
Stromtragfähigkeit der Signalanschlüsse	2 A
Current carrying capacity of the supply connections	9 A
Bemessungswert der galvanischen Trennung	500 V
Funktional getrennte Potentialgruppen	Kontakt/Kontakt
Isolationswiderstand	1000 MΩ
Signal characteristic	PNP
Indicators	LED (A, B) yellow: Signal status (2 x per contact); LED (U) green: Sensor/actuator box status

Connection data

Connection technology: inputs / outputs	6 x M12 connectors, 5 poles, incl. PE
Anschlussstechnik: Stammleitung	1 x Stecker M23; 19-polig

Geometrical Data

Width	60 mm / 2.362 inch
Height	34 mm / 1.339 inch
Depth	123 mm / 4.843 inch

Mechanical data

Mounting type	Screw mounting
---------------	----------------

Material Data

Housing material	PA 66 (UL 94 V0); RAL 7035; silicon and halogen free
Halogen-free	Yes
Materialeigenschaften der Anschlüsse	Contact: CuSn, pre-nickel- and 0.8 μm gold-plated; Tapped bush: Zn diecast nickel-plated; Seal: Viton; Connection cycles: 50
Potting	Fully encapsulated with conformal coating (UL 94 V0)

Environmental Requirements

Surrounding air (operating) temperature	-25 ... 80 °C
Degree of protection	IP67

Degree of pollution (5)	3 acc. to VDE 0110
Vibration resistance	acc. to IEC 60068-2-6
Shock resistance	acc. to IEC 60068-2-27

Commercial data

Country of origin	DE
GTIN	4050821054337
Customs Tariff No.	85366990990

Approvals / Certificates

UL-Approvals

Logo	Approval	Certificate name
	UL International Germany GmbH (ORDINARY LOCATIONS)	E175199 Sec.5

Compatible products

wiring and connectors

	Item no.: 756-3203/190-050 Connecting cable; straight; 19-pole; 5 m; fitted on one end (with free end); M23 socket, straight	www.wago.com/756-3203/190-050
	Item no.: 756-3203/190-100 Connecting cable; straight; 19-pole; 10 m; fitted on one end (with free end); M23 socket, straight	www.wago.com/756-3203/190-100
	Item no.: 756-3203/190-150 Connecting cable; straight; 19-pole; 15 m; fitted on one end (with free end); M23 socket, straight	www.wago.com/756-3203/190-150
	Item no.: 756-3204/190-050 Connecting cable; angled; 19-pole; 5 m; fitted on one end (with free end); M23 socket, straight	www.wago.com/756-3204/190-050
	Item no.: 756-3204/190-100 Connecting cable; angled; 19-pole; 10 m; fitted on one end (with free end); M23 socket, straight	www.wago.com/756-3204/190-100
	Item no.: 756-3204/190-150 Connecting cable; angled; 19-pole; 15 m; fitted on one end (with free end); M23 socket, straight	www.wago.com/756-3204/190-150

General accessories

	Item no.: 756-8102 M12 protective cap; for unused sockets	www.wago.com/756-8102
	Item no.: 757-060 Spacer module for sensor/actuator box; 6-way	www.wago.com/757-060

Marking accessories

	Item no.: 210-110 Fiber-tip pen	www.wago.com/210-110
	Item no.: 757-011 Marker card; not stretchable; snap-on type	www.wago.com/757-011

Downloads

Documentation

Additional Information

Disposal; Electrical and electronic equipment, Packaging	Oct 15, 2018	265.8 kB	Download
--	--------------	----------	----------

System Description

Sensor/Actuator Boxes – General Product Information	Jun 6, 2017	357.7 kB	Download
---	-------------	----------	----------

smartDATA

CAD data

3D Download 757-165	URL	Download
---------------------	-----	----------

Subject to changes.