

# Active Probe for SMDs

## P6245 • P6243 Datasheet



P6243

### Features & Benefits

#### P6245

- $\geq 1.5$  GHz Bandwidth (Typical, Probe Only)
- $\leq 1$  pF Input Capacitance
- $1 \text{ M}\Omega$  Input Resistance
- Direct Access to SMDs as Small as 0.5 mm Pitch
- Measures CMOS, BiCMOS, ECL, GaAs, and TTL Logic

#### P6243

- 1 GHz Bandwidth (probe only)
- $\leq 1$  pF Input Capacitance
- $1 \text{ M}\Omega$  Input Resistance
- Direct Access to SMDs as Small as 0.5 mm Pitch
- Measures CMOS, BiCMOS, ECL, GaAs, and TTL Logic
- Low-mass Probe Head/Cable
- No Additional Power Supplies or Cables Are Required with TEKPROBE™ BNC Interface

### Applications

- High-speed Digital Systems Design
- Component Design/Characterization
- Manufacturing Engineering and Test
- Educational Research

## P6245 and P6243 Active Probes for TEKPROBE BNC Interfaces

### P6245

The P6245 Active FET probe achieves high-speed signal acquisition by solving three traditional problems:

- Lower DUT loading ( $\leq 1$  pF/1 M $\Omega$  probe loading)
- Direct and easy access to SMDs
- Access DUT signals and scope bandwidth for TDS600/700/3000/5000/6000/7000\*1 and CSA7000 scopes up to 1 GHz bandwidths

The P6245 and P6243 Active probes provide the electrical and mechanical performance required for today's digital systems designs. No additional power supplies or cables are required when used with TEKPROBE BNC oscilloscopes. Both the P6245 and P6243 achieve high-speed signal acquisition and low circuit loading, required for solving today's problems faced by designers.

The small compact probe head and versatile attachment accessories allow direct connection to the device under test.

The P6245 and P6243 Active Probes provide scope bandwidth at the probe tip for the TDS500/600/700; the P6243 provides scope bandwidth at the probe tip for the TDS3000 Series scope up to 1 GHz bandwidth.

\*1 Some TDS6000 or TDS7000 oscilloscopes require a TCA-BNC adapter.

### P6243

The P6243 Active FET probe is the high-performance probing solution for 500 MHz oscilloscopes. The P6243 has a probe only bandwidth of 1 GHz and will provide a 500 MHz system bandwidth when used with Tektronix' full line of 500 MHz oscilloscopes. In addition, the P6243 is powered by the TEKPROBE BNC interface, eliminating the need for additional power supplies and cables when used with TEKPROBE BNC oscilloscopes.

The P6243 offers superior signal acquisition on surface mount devices compared to the much higher capacitive loading of passive probes. The P6243 has  $\leq 1$  pF capacitive loading which allows it to measure high-speed signals without affecting the signal or device under test. Furthermore, the included accessories and adapters allow for easy attachment to SMDs.

## Characteristics

Probe Type	P6243	P6245
Cable Length	1.3 m	1.3 m
Attenuation	10X	10X
Bandwidth in GHz (Probe Only)	1 GHz	1.5 GHz
Rise Time	<350 ps	<250 ps
Input C in pF	$\leq 1$ pF	$\leq 1$ pF
Input R in $\Omega$	1 M $\Omega$	1 M $\Omega$
Linear Dynamic Range	$\pm 8$ V	$\pm 8$ V
DC Offset Range	N/A	10 V
Max Voltage (Nondestruct) (DC+PkAC)	$\pm 15$ V	$\pm 15$ V
Propagation Delay	5.3 ns $\pm 200$ ps	5.3 ns $\pm 200$ ps

## Ordering Information

### P6245

Active Probe.

### P6243

Active Probe.

### Included Accessories

Description	Quantity P6245	Quantity P6243	Reorder Part Number
Solderable Probe Tips	10 each	10 each	131-5638-xx (Pkg. of 10)
1 in. Ground Lead	2 each	2 each	196-3439-xx (Pkg. of 10)
6 in. Ground Lead	2 each	1 each	196-3436-xx
3 in. Ground Lead	2 each	1 each	196-3437-xx
Y Lead Adapters	2 each	1 each	196-3463-xx
SMT KlipChip™ Adapter	4 each	2 each	206-0364-xx
Color Coding Clips, 2 each 5 colors	1 each	1 each	016-1315-xx
Right Angle Square Pin Adapter	2 each	1 each	214-4227-xx
100 Mil Square Pin Adapter	2 each	1 each	131-5777-xx

### Service

Opt. C3 – Calibration Service 3 Years

Opt. C5 – Calibration Service 5 Years

Opt. D1 – Calibration Data Report

Opt. D3 – Calibration Data Report 3 Years (with Opt. C3)

Opt. D5 – Calibration Data Report 5 Years (with Opt. C5)

Opt. R3 – Repair Service 3 Years

Opt. R5 – Repair Service 5 Years

Opt. SILV400 – Standard Warranty Extended to 5 Years (P6243).

Opt. SILV600 – Standard Warranty Extended to 5 Years (P6245).

### Recommended Accessories

#### SMD Probing Adapters\*1

SureFoot® Adapters –

50 mil pitch. Order SF501.

25 mil and 0.65 mm pitch. Order SF502.

0.5 mm pitch. Order SF503.










IC Grabber – 0.5 mm pitch. Order 013-0309-00 (See SureFoot Adapters).

\*1 See SureFoot for complete SMD Adapters information.

Please see the General Customer Information pages for additional information.




P6245 / P6243  
Part Reorder 1-800-833-9200

 <p>131-5777-xx 100 mil Square Pin Ground Adapter</p>	 <p>214-4227-xx Right Angle Square Pin Adapter</p>	 <p><b>Tektronix</b> SF503 Solderless PROBE 0.5 mm SET OF 12 PAT. 5,387,872</p>	 <p><b>Tektronix</b> SF502 Solderless PROBE 25mil SET OF 12 PAT. 5,387,872</p>	 <p><b>Tektronix</b> SF501 Solderless PROBE 90mil SET OF 12 PAT. 5,387,872</p>
 <p>131-5638-xx Solderable Probe Tips</p>		 <p>016-1315-xx Color Coding Clips</p>		
 <p>206-0364-xx (1 each) SMT KlipChip</p>				
 <p>196-3410-xx Ground Lead set</p> <p>6" Ground Leads 196-3436-xx</p> <p>1" Z Ground Leads 196-3439-xx</p> <p>3" Ground Leads 196-3437-xx</p> <p>Y-Leads 196-3463-xx</p>				



SF500 Series (Surefoot)



IC Grabber 013-0309-00



Tektronix is registered to ISO 9001 and ISO 14001 by SRI Quality System Registrar.

**Contact Tektronix:**

- ASEAN / Australasia** (65) 6356 3900
- Austria** 00800 2255 4835\*
- Balkans, Israel, South Africa and other ISE Countries** +41 52 675 3777
- Belgium** 00800 2255 4835\*
- Brazil** +55 (11) 3759 7627
- Canada** 1 800 833 9200
- Central East Europe and the Baltics** +41 52 675 3777
- Central Europe & Greece** +41 52 675 3777
- Denmark** +45 80 88 1401
- Finland** +41 52 675 3777
- France** 00800 2255 4835\*
- Germany** 00800 2255 4835\*
- Hong Kong** 400 820 5835
- India** 000 800 650 1835
- Italy** 00800 2255 4835\*
- Japan** 81 (3) 6714 3010
- Luxembourg** +41 52 675 3777
- Mexico, Central/South America & Caribbean** 52 (55) 56 04 50 90
- Middle East, Asia, and North Africa** +41 52 675 3777
- The Netherlands** 00800 2255 4835\*
- Norway** 800 16098
- People's Republic of China** 400 820 5835
- Poland** +41 52 675 3777
- Portugal** 80 08 12370
- Republic of Korea** 001 800 8255 2835
- Russia & CIS** +7 (495) 7484900
- South Africa** +41 52 675 3777
- Spain** 00800 2255 4835\*
- Sweden** 00800 2255 4835\*
- Switzerland** 00800 2255 4835\*
- Taiwan** 886 (2) 2722 9622
- United Kingdom & Ireland** 00800 2255 4835\*
- USA** 1 800 833 9200

\* European toll-free number. If not accessible, call: +41 52 675 3777

Updated 10 February 2011

**For Further Information.** Tektronix maintains a comprehensive, constantly expanding collection of application notes, technical briefs and other resources to help engineers working on the cutting edge of technology. Please visit [www.tektronix.com](http://www.tektronix.com)



Copyright © Tektronix, Inc. All rights reserved. Tektronix products are covered by U.S. and foreign patents, issued and pending. Information in this publication supersedes that in all previously published material. Specification and price change privileges reserved. TEKTRONIX and TEK are registered trademarks of Tektronix, Inc. All other trade names referenced are the service marks, trademarks, or registered trademarks of their respective companies.

27 Jul 2012

60W-13989-6

