
NIGHT BREAKER UNLIMITED

Halogen headlight lamps for cars



Areas of application

- Headlight

Product benefits

- Up to 110 % more light on the road (compared to standard halogen lamps)
- Up to 40 m longer beam of light (compared to standard halogen lamps)
- Up to 20 % whiter light (compared to standard halogen lamps)
- Drivers spot obstacles and dangerous situations much sooner
- Optimum light for more time to react
- Patented blue ring coating for less reflected glare
- More efficient light production thanks to optimized inert filling gas formula
- Higher resilience due to robust coil design

Product features

- Eye-catching design with partial blue coating and silver cap

Product family datasheet

Technical data

Product description	Electrical data				Photometrical data		Dimensions & weight	
	Power input	Nominal wattage	Nominal voltage	Test voltage	Luminous flux	Luminous flux tolerance	Length	Diameter
64150NBU	68 W ¹⁾	55.0 W	12.0 V	13.2 V	1550 lm	±15 %	67.5 mm	9 mm
64151NBU	68 W ¹⁾	55.0 W	12.0 V	13.2 V	1450 lm	±15 %	42.0 mm	11.0 mm
64193NBU	75 / 68 W ¹⁾		12.0 V	13.2 V	1650/1000 lm	±15 %	82.0 mm	13.0 mm
-	75 / 68 W ¹⁾		12.0 V	13.2 V	1650/1000 lm	±12 / ±15 %	82.0 mm	13.0 mm
64210NBU	58 W ¹⁾	55.0 W	12.0 V	13.2 V	1500 lm	±10 %	59.0 mm	12.0 mm
-	58 W ¹⁾	55.0 W	12.0 V	13.2 V	1500 lm	±10 %	59.0 mm	12.0 mm
64211NBU	62 W ¹⁾	55.0 W	12.0 V	13.2 V	1350 lm	±10 %	67.0 mm	12.0 mm
9005NBU	73 W ¹⁾	60.0 W	12.0 V	13.2 V	1860 lm	±12 %	80.3 mm	12.0 mm
9006NBU	62 W ¹⁾	51.0 W	12.0 V	13.2 V	1095 lm	±15 %	80.3 mm	12.0 mm
NBU	68 W ¹⁾	55.0 W	12.0 V	13.2 V	1550 lm	±15 %	67.5 mm	9 mm
NBU	68 W ¹⁾	55.0 W	12.0 V	13.2 V	1450 lm	±15 %	42.0 mm	11.0 mm
NBU	62 W ¹⁾	55.0 W	12.0 V	13.2 V	1350 lm	±10 %	67.0 mm	12.0 mm

Product description	Lifespan		Additional product data	Certificates & standards	Country specific categorizations
	Lifespan B3	Lifespan Tc	Base (standard designation)	ECE category	Order reference
64150NBU	150 h	300 h	P14.5s	H1	64150NBU 55W 12
64151NBU	150 h	300 h	PK22s	H3	64151NBU 55W 12
64193NBU	80 / 260 h ²⁾	160 / 400 h ²⁾	P43t	H4	64193NBU 60/55W
-	250 / 400 h ²⁾	500 / 900 h ²⁾	P43t	H4	64193NBU 60/55W
64210NBU	150 h	250 h	PX26d	H7	64210NBU 55W 12
-	330 h	550 h	PX26d	H7	64210NBU 55W 12

Product family datasheet

Product description	Lifespan		Additional product data	Certificates & standards	Country specific categorizations
	Lifespan B3	Lifespan Tc	Base (standard designation)	ECE category	Order reference
64211NBU	150 h	250 h	PGJ19-2	H11	64211NBU 55W 12
9005NBU	280 h	550 h	P20d	HB3	9005NBU 60W 12V
9006NBU	860 h	1720 h	P22d	HB4	9006NBU 51W 12V
NBU	400 h	650 h	P14.5s	H1	64150NBU 55W 12
NBU	400 h	650 h	PK22s	H3	64151NBU 55W 12
NBU	350 h	580 h	PGJ19-2	H11	64211NBU 55W 12

¹⁾ Maximum

²⁾ Filament 1

Product family datasheet

Application advice

For more detailed application information and graphics please see product datasheet.

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.