


<b>Order code</b>	<b>Manufacturer code</b>	<b>Description</b>
33-1027	n/a	BLUE 3MM FORK TERMINAL PK100 (RC)

	Page 1 of 2
The enclosed information is believed to be correct, Information may change without notice due to product improvement. Users should ensure that the product is suitable for their use. E. & O. E.	Revision A 20/02/2007

30-01-2001

DRAWING  
SCALE SIZE: N/A

SHEET 2 of 12

**INSULATED FORK / SPADE TERMINALS**

Working Voltage 600 V. Max AC or DC  
 Working Temperature -40 To +85 Deg C  
 Basic Tolerance  $\pm 0.5$  mm  
 Insulation Vinyl

For Further Technical Specification  
 Refer To DAV 1069 Sheets 1 To 4

Davico Part No.	Stud Size	D (mm)	E (mm)	F (mm)	L (mm)	T (mm)	W (mm)	d1 (mm)	d2 (mm)
ERF3N	3 mm	4.0	10.0	6.5	21.0	0.75	5.7	1.7	3.7
ERF4N	4 mm	4.0	10.0	6.5	21.0	0.75	6.4	1.7	4.3
ERF5	5 mm	4.0	10.0	6.5	21.0	0.75	8.1	1.7	5.3
EBF3I	6 mm	4.5	10.0	6.5	21.0	0.80	5.7	2.3	3.2
EBF4N	8 mm	4.5	10.0	6.5	21.0	0.80	6.4	2.3	4.3
EBF5	10 mm	4.5	10.0	6.5	21.0	0.80	7.9	2.3	5.3
EYF3	3 mm	6.3	13.0	7.0	25.5	1.00	8.3	3.4	3.7
EYF4N	4 mm	6.3	13.0	7.0	25.5	1.00	8.3	3.4	4.3
EYF5	5 mm	6.3	13.0	7.0	25.5	1.00	9.0	3.4	5.3

# DAVICO

Keeping electricity firmly in its place.

REV	DATE	SIG.
1		
2		
3		