



SINAMICS LINE REACTOR FOR POWER MODULE FSD 18.5 AND 22 KW, RATED POWER BASED ON I_L FOOT PRINT

Figure similar

Order number	6SL3203-0CJ24-5AA0
Phase number / of the input voltage	3
Type of voltage / of the input voltage	AC
Input voltage	380 ... 480
Output current / Rated value	47 A
Active power loss	
• at 50 Hz	Wert fehlt!
• at 60 Hz	Wert fehlt!
Type of electrical connection	
• for mains supply line	screw-type terminal
• for load-side outgoing feeder	Cable
Type of connectable conductor cross-section / for load-side outgoing feeder	Wert fehlt!
Connectable conductor cross-section	
• for mains supply line	16 mm ²
• for load-side outgoing feeder	16 mm ²
Cable length / of connecting cable / for load-side outgoing feeder	0.7 m
Type of electrical connection / for PE conductor	M8 Screw
Protection class IP	IP20
Width	275 mm
Height	455 mm
Depth	84 mm
Net weight	13 kg
Certificate of suitability	cURus

Further information

Information und Download Center

https://www.automation.siemens.com/mcms/infocenter/content/en/Pages/order_form.aspx

Technical documentation

<http://w3.siemens.com/mcms/mc-solutions/en/motion-control/support/technical-documentation/Pages/technical-documentation.aspx>

Industry Mall

<https://eb.automation.siemens.com/mall/en/WW/Catag/Product/6SL32030CJ245AA0/all>

Industry Online Support

<http://support.automation.siemens.com/WW/view/en/6SL32030CJ245AA0/all>