



Datenblatt - Fiche technique - Data sheet

11.04.5352




ROLINE VGA-Kabel HD15 ST - BU mit Ferritkern, 2,0m

ROLINE HD15 M/HD15 F avec noyaux de ferrite, 2,0m

ROLINE HQ VGA Cable + Ferrite, HD15, M/F, 2 m

CUSTOMER NO:	REMARK




NOTE:

- 1) PRIMARY DIM:A,C,D
- 2) FULLY COPPER FOIL SHIELD 360°.
- 3) CABLE AND MODEL COLOR:BLACK
- 4) RoHS COMPLIANT

14	NON UL PVC TUBE OD:2.3MM BLACK 6PCS RoHS
13	UL HEAT SHRINK TUBE BLACK OD:1.5mm RoHS 6PCS
12	UL HEAT SHRINK TUBE BLACK OD:3.0mm RoHS 6PCS
11	SOLDER WIRE RoHS
10	CABLE TIE BLACK 12cm RoHS
9	COPPER W:0.024M RoHS 2PCS
8	JUMP WIRE 24AWG 3CM RoHS
7	FERRITE CORE $\phi 17.5 \times 28.5 \times 9.5$ mm RoHS
6	SCREW: #4-40UNC E:40.2MM BLACK(1101) RoHS
5	INNER JACKET PE RoHS
4	OUTER JACKET PVC 45Pa BLACK(1101) RoHS
3	HDB15F BLUE SOLDER TYPE TERMINAL PLATED GOLD FLASH RoHS
2	HDB15M BLUE SOLDER TYPE TERMINAL PLATED GOLD FLASH W/O 9PIN RoHS
1	UL2919 28#*3COAX+28#*7C+AL+MY+B(1/65%)+D BALCK(1101) OD:8.0MM LENGTH RoHS



PINOUT:



A	FIRST EDITION	He X.Lin	18/04/09																								
REV. ECR	DESCRIPTION	C.N.	DATE																								
<small>THIS DRAWING AND SPECIFICATIONS ARE THE PROPERTY OF ROTRONIC CO., LTD. ANY REPRODUCTION OR USE WITHOUT THE WRITTEN CONSENT OF ROTRONIC CO., LTD. IS PROHIBITED.</small>		<h1>Rotronic Co., Ltd</h1>																									
<small>UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS APPROX. TOLERANCES AS FOLLOWS</small>		<h2>MONITOR CABLE</h2>																									
<table border="1"> <tr> <th>DIMENSIONS</th> <th>TOLERANCE</th> </tr> <tr> <td>0.01 TO 30.00mm</td> <td>± 0.10mm</td> </tr> <tr> <td>30.01 TO 80.00mm</td> <td>± 0.15mm</td> </tr> <tr> <td>80.01 TO 100.00mm</td> <td>± 0.20mm</td> </tr> <tr> <td>100.01mm</td> <td>± 0.30mm</td> </tr> </table>	DIMENSIONS	TOLERANCE	0.01 TO 30.00mm	± 0.10 mm	30.01 TO 80.00mm	± 0.15 mm	80.01 TO 100.00mm	± 0.20 mm	100.01mm	± 0.30 mm	<table border="1"> <tr> <td>CHD.</td> <td>CON.</td> </tr> <tr> <td>HE X.LIN</td> <td>APPL</td> </tr> </table>	CHD.	CON.	HE X.LIN	APPL	<table border="1"> <tr> <td>PART NO.</td> <td>W28SBK1MFXK</td> </tr> <tr> <td>WORK SHEET</td> <td>1/2</td> </tr> <tr> <td>UNIT</td> <td>MM</td> </tr> <tr> <td>SIZE</td> <td>A4</td> </tr> <tr> <td>REV.</td> <td>A</td> </tr> </table>		PART NO.	W28SBK1MFXK	WORK SHEET	1/2	UNIT	MM	SIZE	A4	REV.	A
DIMENSIONS	TOLERANCE																										
0.01 TO 30.00mm	± 0.10 mm																										
30.01 TO 80.00mm	± 0.15 mm																										
80.01 TO 100.00mm	± 0.20 mm																										
100.01mm	± 0.30 mm																										
CHD.	CON.																										
HE X.LIN	APPL																										
PART NO.	W28SBK1MFXK																										
WORK SHEET	1/2																										
UNIT	MM																										
SIZE	A4																										
REV.	A																										
WFM-ED-07E																											

CUSTOMER NO:	REMARK

客戶料號	長度(M)	包裝方式	紙箱尺寸			裝箱數量
			高(cm)	長(cm)	寬(cm)	
11.04.5352	2.0	吊卡+PE袋(8*10*0.08mm)	20	37	30	20
11.04.5353	3.0	吊卡+PE袋(8*10*0.08mm)	17	46	30	20
11.04.5356	6.0	吊卡+PE袋(8*10*0.08mm)	17	46	30	10
11.04.5360	10	PE袋(9*14*0.08mm)	20	32.5	25	5
11.04.5370	20	PE袋(12*14*0.08mm)	18	26	26	2
11.04.5380	30	PE袋(14*16*0.08mm)	18.5	36.5	30	2



- NOTE:
- 1)線材長度和PE BAG規格參表格.
 - 2)貼紙由業務提供.
 - 3)各長度的線材,紙箱尺寸和裝箱數量參上表格.
 - 4)產品符合RoHS標準.

A	FIRST EDITION	He X.Lin	18/04/09
REV. ECR	DESCRIPTION	C.N.	DATE
<small>THIS DRAWING AND SPECIFICATIONS ARE THE PROPERTY OF ROTRONIC CO. LIMITED AND SHALL NOT BE REPRODUCED OR USED IN ANY MANNER WITHOUT THE WRITTEN CONSENT OF ROTRONIC CO. LIMITED.</small>		Rotronic Co., Ltd	
<small>UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS (INCHES) TOLERANCES ARE:</small>		MONITOR CABLE	
<small>DIMENSIONS</small> 0.00 TO 20.00mm 20.01 TO 50.00mm 50.01 TO 100.00mm 100.01mm	<small>TOLERANCES</small> ±0.10mm ±0.15mm ±0.15mm ±0.20mm	<small>DRWD.</small> He X.Lin	<small>APP.</small>
<small>MATERIAL</small> FRSH		<small>PART NO.</small> W28SBK1MPXX	<small>REV.</small> A
<small>SCALE</small>		<small>SHEET</small> 2/2	<small>SIZE</small> A4