

RTT750HR.NX900



Article Number: 115-00001

Releasable Cable Tie, 29.6" Long, 200 lb Tensile Strength, PA66, Yellow, 5/pkg



Download spec sheet

Base Data

Local Order Number	RTT750HR.NX900
Type	SpeedyTie (RTT750HR)
Color	Red (RD) Yellow (YE)
Features and Benefits	<ul style="list-style-type: none"> • The heavy duty Speedy tie features a specially designed head and patented trigger to allow for repeated use in temporary bundling applications. • Additional design feature on the head allows excess strap to be tucked away after installation.
Product Description	HellermannTyton releasable cable ties offer a release feature in the head allowing for easy access to wire bundles when changes or temporary bundling are necessary. The head design guarantees high tensile strength even after repeated use.
Short Description	Releasable Cable Tie, 29.6" Long, 200 lb Tensile Strength, PA66, Yellow, 5/pkg

Product Dimensions

Minimum Tensile Strength (Imperial)	200.0 lbs
Minimum Tensile Strength (Metric)	888.0 N
Length L (Imperial)	29.6 "
Length L (Metric)	752.0 mm
Fixation Method	None
Identification Plate Position	none
Releasable Closure	Yes
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.51 "
Width W (Metric)	13.0 mm
Bundle Diameter Min. (Imperial)	1.6 "
Bundle Diameter Min. (Metric)	40.0 mm
Bundle Diameter Max. (Imperial)	8.3 "
Bundle Diameter Max. (Metric)	210 mm
Thickness T (Imperial)	0.075 "
Thickness T (Metric)	1.9 mm

Logistics and Packaging

Quantity Per	bag
Package Quantity (Metric)	5 Pieces

Carton Quantity 60 Pieces

Weight (Metric) 23.2 kg

Material and Specifications

Material Polyamide 6.6 (PA66)

Material Shortcut PA66

Flammability UL94 V2

Operating Temperature -40°F to +185°F (-40°C to +85°C)

ROHS Compliant Yes