

PSEN ma1.4p-57/PSEN ma1.4-10mm/ 1unit**Product number:****506339**

Product version:	1.0
Approvals:	CE, cULus Listed, TÜV
Sensor principle:	magnetic
Number of N/O:	2
Connection type:	M8, 8pol. male
Switching voltage:	24 V
Type of switching voltage:	DC
Assured switching distance:	10.0 mm
Assured release distance:	22 mm
Protection type, housing:	IP6K9K
Status indicator:	With LED
Design:	square
Width dimension:	26.0 mm
Height dimension:	37.0 mm
Depth dimension:	18.0 mm
Gross weight:	68 g

Net weight:	32 g
Ambient temperature:	-10 - 55 °C