

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1300540020](#)  
**Status:** **Active**  
**Overview:** Brad Industrial Ethernet Solutions  
**Description:** Ultra-Lock (M12) D-Coded to RJ-45 Adapter, Straight to Straight, 4-Pole Female to RJ45 Male, Unshielded PVC, 0.050m (1.97") Length

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

UL E200650

**General**

Product Family Industrial Receptacles  
 Series [130054](#)  
 IP Rating IP67  
 Overview [Brad Industrial Ethernet Solutions](#)  
 Product Name RJ45, Ultra-Lock (M12)  
 Taxonomy Circular Industrial Connectors  
 Type Double Ended  
 UPC 78678804286

**Physical**

Coupling Type Push to Lock  
 Gender Female-Male  
 Keyway D-coded  
 Length 0.50m  
 Material - Component Nickel-plated Brass  
 Mounting Thread Size PG9  
 Net Weight 51.709/g  
 Orientation Straight  
 Panel Mount Back  
 Poles 4  
 Temperature Range - Operating -25° to +80°C  
 Wire Size AWG 24  
 Wire/Cable Type Unshielded PVC

**Electrical**


Current - Maximum per Contact 0.5A  
 Voltage - Maximum 250V AC/DC

**Material Info**

Engineering Number ERWPAB3002M005

**Reference - Drawing Numbers**

Sales Drawing SD-130054-002-001



Series image - Reference only

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant with Exemption 6(c)**

**REACH SVHC**

Contained Per - D(2021)4569-DC (8 July 2021)

Lead

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

ZZCERT\_CE -

Declaration of

Conformity

ZZCERT\_UKCA

- Declaration of

Conformity

**China RoHS**

50 Image

Not Relevant

Not Contained

CER\_4000408918\_00\_000.pdf

CER\_4000410285\_00\_000.pdf

**Search Parts in this Series**

[130054 Series](#)