

## collet chuck DIN 6343 173 E, round

**ORION**<sup>®</sup>

### Execution:

- hardened and ground
- clamping bridge max. 0.1 mm of the nominal diameter
- Concentricity
- $\varnothing$  1-10 mm  $\leq$  20  $\mu$ m
- $\varnothing$  11-30 mm  $\leq$  30  $\mu$ m
- $\varnothing$  31-60 mm  $\leq$  40  $\mu$ m
- up to  $\varnothing$  8 mm smooth bore, from  $\varnothing$  9 mm with crosswise grooves
- Other designs and complete sets can be supplied on request.



<b>Art. no.</b>	<b>23353 090</b>
<b>Brand</b>	ORION
<b>Manufacturer Part Number</b>	23353090
<b>Outer diameter</b>	60 mm
<b>Diameter</b>	48 mm
<b>Length</b>	94 mm
<b>Clamping diameter</b>	9 mm
<b>Profile shape</b>	Round with transverse grooves
<b>DIN</b>	173
<b>Diameter 2</b>	48 mm
<b>Gross Weight</b>	0.649 kg
<b>Product Group</b>	2AE

### EAN

4053625355082