

Horizontal quick-action clamp

With open clamping arm and angular base



Application:


For quick and secure clamping on machine tables and appliances.

Version:

- Galvanised and passivated
- With red oil-resistant plastic handle
- Case-hardened and lubricated bearing bushes
- Stainless steel rivet
- Ergonomic, oil-resistant handle with large hand rest and soft components
- Protection against the loss of the clamping screw on the end of the clamping arm

Delivery:

With tempered and galvanised thrust bolt



Art. no.	26216 030
Size	3
Hole distance	24 mm
Hole distance 2	28.5 mm
Bore diameter	6.8 mm
Clamping height	70 mm
Retaining force	1800 N
Max. tensile force	2500 N
Height	86.5 mm
Length	206 mm
Thumbscrew size	M8 x 45 mm

EAN-Code

4020772093334