

Electronic micrometer

Disc-shaped measuring faces

ORION®

Application:

For measuring tooth span (Wk) on cogs as of module 0.5, for recesses, groove distances etc.

Execution:

- Measuring faces made of hardened steel
- Advanced friction coupling for consistent, repeatable measuring force
- ON/OFF
- Zero setting at any position
- mm/inch switch-over
- ABS function

Delivery:

In a case, with battery (1 x 1.5 V type SR44)



Art. no.	31610 005
Brand	ORION
Manufacturer Part Number	31610005
Display	Digital
Min./max. length measuring range	0-25 mm
Digit increment	0.001 mm
Measuring surface diameter	20 mm
Measuring arrangement	Plate
Material of measuring bolt	Steel
IP protection class	IP 40
Spindle clamping	Yes
Functions	On/Off, With zero setting at any position, With mm / inch switching, ABS function
Min./max. measurement force	5-10 N
Number of rechargeable batteries/batteries	1 PCS
Battery designation	1,5 V SR44
DIN	863
Measuring spindle increments	0.5 mm
Calibration Group	D
Gross Weight	0.467 kg
Product Group	3BJ

EAN

4039247546411