

Micrometer

With replaceable anvil for special applications

Mitutoyo

Application:

For measuring e.g. the wall thickness of pipes and cylinders

Execution:


- Semi-gloss chrome-plated scale drum and sleeve
- Carbide-tipped measuring faces

Advantage:

- For measuring the wall thickness of cylinders and pipes, as well as openings, slots and hard-to-reach places.

Delivery:

Includes box, setting standard (from 25 mm), adjustment wrench



Art. no.	32016 486
Brand	MITUTOYO
Manufacturer Part Number	117-101
Min./max. length measuring range	0-25 mm
Vernier scale	0.01 mm
Measuring surface diameter	6.3 mm
Measuring spindle increments	0.5 mm
Bracket depth	26.5 mm
Spindle clamping	Yes
Error limit	4 µm
Display	Nonius
Min./max. measurement force	5-10 N
Calibration Group	D
Gross Weight	0.341 kg
Product Group	3MA

EAN

4946368011776