

Flat magnetic grips, hard ferrite core, steel jacket

With threaded bush

ORION[®]

Application:

Auxiliary materials with universal application during clamping, assembling, lifting and welding operations, and for installing in devices etc.

Version:

- With hard ferrite core
- Surface galvanised
- Magnetic shielding
- With threaded bush
- Operating temperature up to 100°C

Art. no.	51145 530
Outer diameter	20 mm
Height	13 mm
Height of the base	6 mm
Thread dimension	M3
Adherence strength	40 N
Thread length	7 mm



EAN-Code

4039247261826