

KFM 18 LTX 3 RF cordless laminate trimmer

metabo®

Application:

Compact metal laminate trimmer for 45° chamfers and radii of 2 to 3 mm on visible edges

Version:

- Oxide-free and burr-free surfaces in ideal preparation for applying powder or paint coatings for maximum corrosion protection
- One-touch controller: Patented tool-free milling depth adjustment in 0.1 mm increments; stop points for short adjustment times which prevent accidental adjustment of cutting depth when working
- Slimline milling head with standard carbide indexable inserts and ball bearing thrust ring for working on pipes and on curved surfaces
- Guide stop for uniform work results and high surface quality when processing straight metal sheets

Advantage:

- Rotatable battery pack for better working in tight spaces
- Removable dust protection filter protects motor from coarse particles

Delivery:

2 each of carbide indexable inserts 45° chamfer, radius R2, radius R3, guide stop, screwdriver, dust filter, additional handle VibraTech, 2 LiHD battery packs, ASC 30-36-V charger, in MetaLoc case



Art. no.	70377 500
Type of rechargeable battery/battery	LiHD
Rechargeable battery/battery capacity	5.5 Ah
Battery included	Yes
Battery voltage	18 V
Max. idle speed	7000 rpm
Max. chamfer height 45°	4 mm
Max. chamfer width 45°	6 mm
With soft start	Yes
With restart protection	Yes
With overload protection	Yes

EAN-Code

4007430293442