

Cordless straight grinder AGSZ 18-90 LBL Select

HighPower lithium-ion 18 volt



Application:

For cutting, grinding, deburring and milling operations

Execution:

- the long, slender neck allows deep insertion in workpieces (e. g. internal grinding of pipes)
- innovative collet chucks with circumferential band to protect workpiece
- With electronic rotation speed preselection
- With soft start, restart protection, electronic overload protection and brake

Advantage:

- more flexibility with the FEIN MultiVolt interface.
- Replaceable rubber collar bearing cover
- Effortless work due to slim size, compact design and low weight with good balance

Delivery:

Does not include battery or charger, in plastic case, incl. Collet chuck Ø 6 mm, open-ended spanner SW13 + SW17



Art. no.	71028 816
Model	AGSZ 18-90 LBL Select
Battery voltage	18 V
Battery included	No
Number of rechargeable batteries/batteries	0
Motor design	Brushless motor
Max. clamping diameter	8 mm
Milling cutter diameter max.	12 mm
Sanding block diameter max.	50 mm
Max. idle speed	29000 rpm
Min./max. idle speed	9000-29000 rpm
Weight	1.8 kg
With soft start	Yes
With overload protection	Yes
With restart protection	Yes
With speed pre-selection	Yes
With working lights	Yes
Product Group	Prod. Gr. 704

EAN

4014586888750