

Ring bolt

Screwable sling point, 360° rotation

CARTEC

Application:

For the safe attachment of loads.

Execution:

- Forged, high-strength annealed
- 100% Magnaflux crack-tested in accordance with DIN EN 1677-1
- captive hexagon socket screw,
- can be rotated 360°
- designed for up to 20,000 strokes at full load
- Powder-coated surface: salmon-coloured

Advantage:

- 4-fold safety
- Can be set in the direction of force to avoid accidental unscrewing or overscrewing



Art. no.	77232 130
Brand	CARTEC
Manufacturer Part Number	C807XHT30
Design	Without key
Thread dimension	M30
Load-carrying capacity	4.5 t
Distance between lower edge of retainer holder and retainer	86 mm
Bracket width	28 mm
Bracket height	25.5 mm
Outer diameter	111 mm
Diameter 2	75 mm
Internal width	60 mm
Width of support plate	66 mm
Usable thread length	45 mm
Width across flats	17 mm
Weight	2 kg
Gross Weight	2.000 kg
Product Group	775

EAN

8013429916168