

Permanent NEO lifting magnet

3-fold safety

Application:

For the secure lifting of sheet metals, profiles, panels, round- and bar-shaped parts or for loading and unloading machines.

Advantage:

- Large lifting capacity with low tare weight and small dimensions
- Robust, low-maintenance, user-friendly
- Easy to switch on and off using the hand lever, with safety lock

Delivery:

With test certificate

Art. no.	77301 011
Load-carrying capacity	150 kg
Load-carrying capacity for round materials	65 kg
Tear-off weight certified	470 kg
For min./max. round material diameter	40-100 mm
Suitable for min. sheet metal thickness	2 mm
Surface area length	93 mm
Surface area width	60 mm
Height up to load hook	110 mm
Colour	Orange



EAN-Code

0705632164389