

Wasserpumpenzange Professional



mit Druckknopf

Z 22 0 05

Best.-Nr.	mm	II	○	⊙	SB	
26766	250	10	2	50		5
27415	250	10	2	50	x	5

DIN ISO 8976.

Wasserpumpenzange QuickFix Professional



automatisch

Z 23 1 05

Best.-Nr.	mm	II	○	⊙	SB	
39093	250	10	1 ½	40		1
39095	250	10	1 ½	40	x	5

DIN ISO 8976.

Wasserpumpenzange Industrial



mit Druckknopf

Z 22 0 02

Best.-Nr.	mm	II	○	⊙	SB	
36040	180	7	1	30		5
36987	180	7	1	30	x	1
32352	250	10	2	50		5
34518	250	10	2	50	x	5
36041	300	12	2 ½	63		5
36988	300	12	2 ½	63	x	5

DIN ISO 8976.

Wasserpumpenzange QuickFix Classic



automatisch

Z 23 1 01

Best.-Nr.	mm	II	○	⊙	SB	
39091	250	10	1 ½	40		1
39094	250	10	1 ½	40	x	5

DIN ISO 8976.

Wasserpumpenzange Classic



mit Druckknopf

Z 22 0 01

Best.-Nr.	mm	II	○	⊙	SB	
26764	180	7	1	30		5
27351	180	7	1	30	x	5
26765	250	10	2	50		5
27383	250	10	2	50	x	5
26767	300	12	2 ½	63		5
27384	300	12	2 ½	63	x	5

DIN ISO 8976.

Kraftvorschneider Classic



Z 17 0 01

Best.-Nr.	mm	II		Ø mm	SB	
26757	160	6 ½	16	1.6		5
27372	160	6 ½	16	1.6	x	5
26758	180	7	17	1.8		5
27373	180	7	17	1.8	x	5
26759	200	8	18	2		5
27374	200	8	18	2	x	5

DIN ISO 5748.