



336 Sechskant-Steckschlüssel mit Quergriff.

Klinge Chrom-Vanadium Stahl, durchgehend gehärtet, glanzvernickelt.

Griff Wiha Quergriff.

Anwendung Um hohe Drehmomente ermüdungsarm zu übertragen.

Extra Innenbohrung für überstehende Gewindeschäfte.

Best.-Nr.	Ø	↔	↔	↔	↔
00965	5,5	125	157	100	32
00966	6	125	157	100	32
00967	6	200	232	100	32
00968	7	125	157	100	32
00969	7	200	232	100	32
00970	7	350	382	100	32
00971	8	125	157	100	32
00972	8	200	232	100	32
00973	8	350	382	100	32
00974	9	125	157	100	32
00975	9	200	232	100	32
00977	10	125	157	100	32
00978	10	200	232	100	32
00979	10	230	262	100	32
00980	10	350	382	100	32
00982	11	125	157	100	32
00983	11	230	262	100	32
00985	12	125	157	100	32
00986	12	230	262	100	32
00988	13	125	157	100	32
00989	13	230	262	100	32
00990	13	350	382	100	32

00991	14	125	157	100	32
00992	14	350	382	100	32
00993	15	125	157	100	32
00994	16	125	157	100	32
00995	17	125	157	100	32
00996	17	350	388	120	38