

Mini – Jumpers

1.27mm, 2.00mm, 2.54mm & 5.08mm



1.27mm & 2.00mm		Mini - Jumpers	
<p>JPC – type - top closed -</p> <p>Order Code: JPC – 127 – BL – 55</p>	<p>JPE – type - top open -</p> <p>Order Code: JPE – 200 – BL – 55 Other colours: RD, BU, YL</p>	<p>JPC – type - top closed -</p> <p>Order Code: JPC – 200 – BL – 55</p>	<p>JPH – type - with handle -</p> <p>Order Code: JPH – 200 – BL – 55 Other colours: RD, BU, YL & WH</p>

2.54 mm & 5.08 mm		Mini - Jumpers	
<p>JPE – type top open - commercial type -</p> <p>Order Code: JPE – 254 – BL – 55 Other colours: GR, RD, BU, YL & WH</p>	<p>JPC – type top closed</p> <p>Order Code: JPC – 254 – BL – 55 Other colours: GR, RD, BU, YL & WH</p>	<p>JPH – type with handle</p> <p>Order Code: JPH – 254 – BL – 55 Other colours: GR, RD, BU, YL & WH</p>	<p>JPC – type top closed</p> <p>Order Code: JPC – 508 – BL – 55</p>

2.00 mm Multi - Jumper	2.54 mm Multi - Jumper
<p>Order Code: JPM – xx – 200 – BL – 55 No. of Jumper : 02 to 11</p>	<p>Order Code: JPM – xx – 254 – BL – 55 No. of Jumper : 02 to 10</p>

Non Insulated Wire Shorting Links			
<p>JPW – type 254</p> <p>Order Code: JPW – 254 – 55</p>	<p>JPW – type 508</p> <p>Order Code: JPW – 508 – 55</p>	<p>JPW – type 762</p> <p>Order Code: JPW – 762 – 55</p>	<p>JPW – type 102</p> <p>Order Code: JPW – 102 – 55</p>

Specifications	
<p>Max. current rating</p> <p>1.27 & 2.00mm pitch : 1 A</p> <p>2.54 & 5.08mm pitch : 3 A</p> <p>Insulator resistance 1000 MΩ min.</p> <p>Contact resistance 20 mΩ max.</p> <p>Withstanding voltage 500 V AC</p> <p>Operating temperature - 40°C to +105°C</p>	<p>Contact material JPC, JPE, JPH & JPM: Phosphor Bronze JPW: Brass; Ø 0.51 +0.25/-0.00</p> <p>Plating Jumper & Wire Shorting Links Au plated</p> <p>Insulator material P.B.T. UL 94 V-0 (RoHS compliant)</p> <p>Colour attributes BL = black for Jumpers <i>Standard</i> RD = red BU = blue GR = green WH = white YL = yellow <i>Other colours on request</i></p>