

Order code	Manufacturer code	Description
33-1075	n/a	BLUE 5MM FEMALE BULLET SOCKET PK100 RC

	Page 1 of 2
The enclosed information is believed to be correct, Information may change without notice due to product improvement. Users should ensure that the product is suitable for their use. E. & O. E.	Revision A 20/02/2007

DESCRIPTION

Data Sheets For Standard Industrial Light Duty Terminals

QUALITY SYSTEM No:

DRAWN BY: M.TAMAN


SIGNED:

M. Taman

ISSUE DATE: 30-01-2001

DRAWING SCALE SIZE: N/A

SHEET 6 of 12

**INSULATED MALE BULLETS**

Working Voltage 300 V. Max AC or DC
 Working Temperature -40 To +85 Deg C
 Basic Tolerance ± 0.5 mm
 Insulation Vinyl

For Further Technical Specification
 Refer To DAV 1069 Sheets 1 To 4

Davico Part No.	Bullet Diameter	B (mm)	C (mm)	D (mm)	F (mm)	L (mm)	W (mm)
ERAB 4M	4.0 mm	10.0	1.7	4.0	8.5	21.0	4.0
EBAB 4M	4.0 mm	10.0	2.3	4.5	8.5	21.0	4.0
EBAB 5M	5.0 mm	10.0	2.3	4.5	8.5	21.0	5.0
EYAB 5M	5.0 mm	13.0	3.4	4.5	8.5	23.5	5.0

REV

DATE

SIG.

1

REV

DATE

SIG.

2

REV

DATE

SIG.

3

Keeping electricity firmly in its place.